

Infineon's solutions for multicopters

Introducing a new cost effective system solution to ensure excellent user experience Fly longer, safer & with more value-adding functionalities




Industry-leading full system multicopter solutions

Commercial multicopters have come a long way in recent years, evolving from toys to coastal and event mapping sophisticated programmable aircraft. This provides challenges and opportunities for multicopter manufacturers.

Infineon produces cost effective system solutions for this rapidly growing market thereby ensuring an excellent flight experience and simultaneously meeting the requirements of the end user such as lighter weight, longer flying time, safety, reliability, etc.

Benefits	Offer			
Development effort and cost reduction	 With no or little experience in motor control customers can implement the iMOTION™ motor control IC and take flight Project development effort can be reduced by 30 percent by using reference designs and the DAVE™ platform for microcontroller programming 			
Security and authentication	 Enables authentication of components connected to the system. Safety is secured and product liability protected Brand protection and a secured strong identity are provided by state-of-the-art security products which are easy to integrate 			
Accuracy and easy control	Nultifunctional sensors guarantee an easy, stable, smooth, and accurate control of the multicopter Closed loop control of gimbal motor and sensors enhance the stability of the camera and data transmission when recording videos			
Lighter	> The highly efficient components and an effective flight control make the multicopter lighter resulting in longer flight time			
Collision avoidance	> The 24GHz radar can be used to measure the presence of objects, range, and speed/velocity! And it determines proximity as well as an object's position			
Broad portfolio	> Infineon provides a comprehensive portfolio of semiconductor components for multicopters			



Reliable and durable solutions for multicopters


Flight control						ESC		
Microcontroller	Sensor	DC-DC module	LDO	Low noise ampli (LNA)	fier Microcontroller	Sensor	Intelligent power module	
 > XMC4000 family > XMC1000 family > AURIX™ 	 > Pressure sensor: DPS310 > 24 GHz radar sensor: BGT24MR2, BGT24MTR11/ BGT24MTR12/BGT24LTR11 > Current sensor: TLI4970 	> IFX90121ELV50 > IFX91041EJV33 > IFX91041EJV50	> IFX1117ME > IFX54441EJV > IFX1763XEJV33	 LTE: BGA7H, BGA7BGA7L GPS: BGA524N6, BGA824N6 Wi-Fi: BFP842ESD BFR840L3RHESD, BFR843L3, etc. 	> iMOTION™ IRMCK099	 Hall sensor: TLI4961, TLV4961 Angle sensor: TLI5012B, TLE500 		
Security	Accessory authentication	Joystick	Interface protection diodes	LED driver	MOSFET gate driver	Dual n-channel power MOSFET	Low voltage MOSFETs	
 > OPTIGA™ Trust E SLS32AIA > OPTIGA™ Trust P SLJ52ACA > OPTIGA™ TPM SLB96XX 	 > OPTIGA™ Trust SLS10ERE > OPTIGA™ Trust B SLE95250 	> 3D magnetic sensor: TLV493D	> ESD102 series	> BCR450 > BCR321U > BCR421U	> IRS2301S > 6EDL04N02P > IRS23365 > PX3517	> IR3742, etc. > BSC0925ND, etc.	 > OptiMOS™ 5 series > StrongIRFET™ series 	
	Charger		Battery management					
High voltage MOSFETs	Low voltage MOSFETs	Stand alone PWM controller	Authentication IC		Cell balancing	Lov	voltage MOSFETs	
> 600 V-650 V CoolMOS™ CE > 600 V CoolMOS™ P7 (standard grade)	 OptiMOS™ 5 40 V-80 V in TO-220, SuperSO8 StrongIRFET™ 40 V-75 V 	> ICE2QS03G	Direc		OptiMOS™ 30 V in SSO8, S3 DirectFET™ StrongIRFET™ 30 V	ctFET™ S3O8, D		
Gimbal control								
Microcontroller	Angle sensor	LDO	CAN transceiv	er Low volta	GO MUSEFIS	n-channel er MOSFET	MOSFET gate driver	
> XMC1400 family	> TLI5012B > TLE5009	> IFX1117ME > IFX54441EJV > IFX1763XEJV33	> HS CAN IFX1050G > IFX1050GVIO	> OptiMOS™ > StrongIRFI	' 5 25 V-30 V	363TRPBF, etc. > I	R2101STRPBF, etc.	

Demoboards

To shorten customer development cycle time and cost we offer a wide range of application kits:







To get further information on our components for multicopter system solutions visit: www.infineon.com/multicopter www.infineon.com/evaluationboards

Published by Infineon Technologies Austria AG 9500 Villach, Austria

© 2017 Infineon Technologies AG. All Rights Reserved.

Order Number: B131-I0171-V3-7600-EU-EC-P Date: 10/2017

Please note

THIS DOCUMENT IS FOR INFORMATION PURPOSES ONLY AND ANY INFORMATION GIVEN HEREIN SHALL IN NO EVENT BE REGARDED AS A WARRANTY, GUARANTEE OR DESCRIPTION OF ANY FUNCTIONALITY, CONDITIONS AND/OR QUALITY OF OUR PRODUCTS OR ANY SUITABILITY FOR A PARTICULAR PURPOSE. WITH REGARD TO THE TECHNICAL SPECIFICATIONS OF OUR PRODUCTS, WE KINDLY ASK YOU TO REFER TO THE RELEVANT PRODUCT DATA SHEETS PROVIDED BY US. OUR CUSTOMERS AND THEIR TECHNICAL DEPARTMENTS ARE REQUIRED TO EVALUATE THE SUITABILITY OF OUR PRODUCTS FOR THE INTENDED APPLICATION.

WE RESERVE THE RIGHT TO CHANGE THIS DOCUMENT AND/OR THE INFORMATION GIVEN HEREIN AT ANYTIME.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by us in a written document signed by authorized representatives of Infineon Technologies, our products may not be used in any life-endangering applications, including but not limited to medical, nuclear, military, life-critical or any other applications where a failure of the product or any consequences of the use thereof can result in personal injury.