



HiRel rad hard non-volatile NOR Flash

Infineon Technologies' HiRel memories perform in the most extreme environments

Infineon Technologies offers the industry's highest performance, low pin-count, radiation hardened by design 512 Mb rad hard Serial NOR flash. The industry standard Quad Serial Peripheral Interface (QSPI) is simple to use with broad ecosystem support. The rad hard NOR Flash family offers 512 Mb densities in a ceramic or plastic package coupled with the flexibility and fast performance required by high reliability applications. Our radiation hardened NOR Flash memories provide an ideal FPGA boot/configuration solution for systems with limited space, low signal pin count requirements, low power and offer flexibility, reliability, and performance well beyond ordinary serial flash devices.

Our HiRel rad hard NOR Flash memories are ideal for platforms requiring fast boot solutions and offer the highest radiation performance for space-grade FPGAs. Depending on image size, the 512 Mb rad hard NOR Flash can typically store 2 boot code images and can load a 200 Mb bitstream in 0.42 seconds. The 512Mb rad hard NOR Flash supports a single QSPI interface in a x4 mode and a single channel SPI mode for legacy support. Both interfaces are supported by modern FPGA devices and utilize standard instruction sets.

FPGA data storage



Key features

Ultimate reliability

- DLAM QML-V/P
- QCI, datapacks
- RHA, WLAT

Product features

- 512 Mb densities
- 133 MHz QSPI data interface
- Single channel SPI mode for legacy support
- TID 300 krad[Si]
- SEL: >80 MeV·cm²/mg [LET] @ 125°C
- SEFI: <2.77e⁻⁵ err/dev·day
- SEU: IMMUNE
- Mil temperature grade
- 68-lead ceramic flat pack
- 100-pin plastic TQFP
- DLAM QML-V/P certified

Key applications

- Space grade FPGA configuration image storage
- Standalone boot code storage for space processors

Differentiated memory portfolio

- Performance
- Density
- Reliability
- Longevity

HiRel rad hard non-volatile NOR Flash

Infineon Technologies' HiRel memories perform in the most extreme environments

Radiation hardened memories

Infineon's HiRel rad hard memory products portfolio consists of the world's most-reliable nonvolatile memory and offers a wide selection of NOR Flash, F-RAM, and SRAM solutions that enhance overall system computing limits, while providing Size, Weight and Power (SWaP) benefits with greater design flexibility to satisfy the needs of today's advanced space systems and beyond.

Key features

- 512 Mb density
- QSPI interface operating up to 133 MHz
- 10k program/erase cycles @ 85°C
- 10 years data retention at 125°C
- 3.3 V supply voltage
- 1.8/3.3 V I/O support
- -55 to +125°C military temperature grade
- 68-pin ceramic quad flat pack or 100-pin plastic TQFP
- DLAM QML-V or QML-P qualified

Radiation performance

- TID: 300 Krad(Si)
- SEL: > 80 MeV.cm²/mg [LET] @ 125°C
- SEU: Immune
- SEFI: < 2.77e⁻⁵ err/dev-day

Support: www.infineon.com/hirelmemory

Parts list

Density	Infineon P/N	Description	Operating temp	Qual. level	Package	TID ¹⁾	SEL ²⁾	SEU ³⁾	SEFI ⁴⁾
512Mb	CYRS17B512-133AZMB	Quad SPI rad hard NOR Flash, plastic package	-55°C to 125°C	Infineon qual	100-pin TQFP	300	> 80	Immune	< 2.77e ⁻⁵
	CYPT17B512-133AZMB	Quad SPI rad hard NOR Flash, plastic package - PROTO	-55°C to 125°C	PROTOTYPE	100-pin TQFP	-	-	-	-
	*5962F2122201PXE	Quad SPI rad hard NOR Flash, plastic package - DLAM	-55°C to 125°C	QML-P	100-pin TQFP	300	> 80	Immune	< 2.77e ⁻⁵
	CYRS17B512-133UZMB	Quad SPI rad hard NOR Flash, plastic package	-55°C to 125°C	Infineon qual	68-pin CQFP	300	> 80	Immune	< 2.77e ⁻⁵
	CYPT17B512-133UZMB	Quad SPI rad hard NOR Flash, plastic package - PROTO	-55°C to 125°C	PROTOTYPE	68-pin CQFP	-	-	-	-
	*5962F2122202VYC	Quad SPI rad hard NOR Flash, plastic package - DLAM	-55°C to 125°C	QML-V	68-pin CQFP	300	> 80	Immune	< 2.77e ⁻⁵

- 1) Total Ionizing Dose [Krad (Si)]
- 2) Single Event Latchup MeV.cm²/mg [LET] @ 125°C
- 3) Single Event Upset [err/bit.day]
- 4) Single Event Functional Interrupt err/dev-day

Note:

* Coming soon - contact factory for details



www.infineon.com/hirel

Published by
Infineon Technologies AG
Am Campeon 1-15, 85579 Neubiberg
Germany

© 2024 Infineon Technologies AG
All rights reserved.

Document number: B119-I1223-V1-7600-NA-EC-P
Date: 06/2024

Please note!

This Document is for information purposes only and any information given herein shall in no event be regarded as a warranty, guarantee or description of any functionality, conditions and/or quality of our products or any suitability for a particular purpose. With regard to the technical specifications of our products, we kindly ask you to refer to the relevant product data sheets provided by us. Our customers and their technical departments are required to evaluate the suitability of our products for the intended application.

We reserve the right to change this document and/or the information given herein at any time.

Additional information

For further information on technologies, our products, the application of our products, delivery terms and conditions and/or prices, please contact your nearest Infineon Technologies office (www.infineon.com).

Warnings

Due to technical requirements, our products may contain dangerous substances. For information on the types in question, please contact your nearest Infineon Technologies office.

Infineon Technologies Components may only be used in life-support devices or systems with the expressed written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.