


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	1
A1	0.18	-	-
D	11.6 BSC		
E	8 BSC		
Øb	0.35	-	0.45
eD / eE	0.8 BSC		
SD / SE	0.4 BSC		

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Dimensioning and tolerancing methods per ASME Y14.5M-1994.