



1) Does not include plastic protrusion which shall not exceed 0.15mm max. per side.

2) Dambar protrusion shall be maximum 0.1mm per side.

3) Fillet and radii: unless otherwise noted all radii are 0.3mm max.

4) All metal surfaces are plated, except area of cut.

5) Datum A & B to be determined at datum H.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0.1; \pm 1^\circ 30'$