


Outer dimension does not include protrusion or intrusion of  $0.15$  max. per side

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances  $\pm 0.05$   $\pm 2^\circ$