



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	2.65
A1	0.05	-	0.2
D	12.7 BSC		
E	10.2 BSC		
E1	7.5 BSC		
$\theta$	0°	-	8°
c	0.22	-	0.32
b	0.35	0.4	0.49
L	0.5	0.8	1.27
e	1.27 BSC		

1) Dimensioning D include mold flash, dimensioning E1 does not include interlead flash or protrusion. interlead flash or protrusions shall not exceed 0.025 mm per side.

2) Dimension b does not include dambar protrusion. allowable dambar protrusion shall be 0.10mm

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensioning and tolerancing per ASME Y14.5M-1994.