


1) Typical metal surface min. X= 7.25, Y= 12.3

All metal surfaces: tin plated, except area of cut

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances $\pm 0,1$; $\pm 1^\circ 30'$