


1) Does not include plastic or metal protrusion of 0.15 max. per side

2) Does not include dambar protrusion of 0.13 max.

3) JEDEC registration MO-137 variation AE.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Drawing according to ISO 8015, general tolerances