



- 1) Does not include plastic or metal protrusion of 0.15 mm max. per side
- 2) Dambar protrusion shall be maximum 0.1 mm total in excess of lead width.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 []

Drawing according to ISO 8015, general tolerances ± 0.05 ; $\pm 1^\circ 30'$