


Bottom view

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.79
A1	0.165	0.24	0.27
A2	0.5 BSC		
A3	0.07 BSC		
A4	0.025 BSC		
D	4.64 BSC		
E	4.64 BSC		
Øb	0.285	0.315	0.345
eD	0.5 BSC		
eE	0.5 BSC		

All dimensions are in units mm  
 The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]  
 Dimensions and tolerances methods per ASME Y14.5-2009.