


SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	3
A1	0.1	-	-
A2	2.57	2.7	2.82
b	0.34	-	0.43
c	0.21	-	0.25
D	28.36	28.46	28.56
E	15.77	16.03	16.28
E1	12.53	12.63	12.73
e	0.8 BSC		
L	0.58	0.79	0.99

1) Dimension "D" does not include mold flash, protrusions or gate burrs. mold flash, protrusions or gate burrs shall not exceed 0.15 mm per end.

2) Dimension "E1" does not include interlead flash or protrusion. interlead flash or protrusion shall not exceed 0.15 mm per side.

3) Dimension b does not include dambar protrusion/intrusion. allowable dambar protrusion shall not exceed 0.15 mm per side.

All dimensions are in units mm

The drawing is in compliance with ISO 128-30, Projection Method 1 [  ]

Dimensioning and tolerancing conform to ASME Y14.5M-1994.