


- 1) Does not include plastic or metal protrusion of 0.15 max. per side
 2) Dambar protrusion shall be maximum 0.1 mm total in excess of lead width
 All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Drawing according to ISO 8015, general tolerances ISO 2768-mk