


Bottom view

SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
A	-	-	0.9
A1	0	-	0.05
D	3 BSC		
E	3 BSC		
b	0.2	0.25	0.3
D2	2.2 BSC		
E2	1.6 BSC		
e	0.5 BSC		
L	0.3	0.4	0.5

All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Dimensioning and tolerancing conforms to ASME Y14.5-1994.