



SYMBOL	DIMENSIONS		
	MIN.	NOM.	MAX.
e	1.27 BSC.		
N	8		
L	0.45	0.5	0.55
b	0.35	0.4	0.45
D2	4.7	4.8	4.9
E2	4.55	4.65	4.75
D	6 BSC		
E	8 BSC		
A	0.7	0.75	0.8
A1	0	0.02	0.05
A3	0.2 REF		
K	0.2 MIN.		

All dimensions are in units mm
 The drawing is in compliance with ISO 128-30, Projection Method 1 []
 Dimensioning and tolerancing conforms to ASME Y14.5M-1994.

