


REV.	DESCRIPTION	ECN	DATE
E4	INITIAL RELEASE	1120_ER7725E	7-18-24



Symbol	Dimensions			
	Inches		Millimeters	
	Min	Max	Min	Max
BL	0.300	0.310	7.62	7.87
BW	0.205	0.215	5.21	5.46
CH		0.097		2.46
LH	0.010	0.020	0.25	0.51
LW1	0.180	0.190	4.57	4.83
LW2	0.068	0.078	1.73	1.98
LL1	0.161	0.171	4.09	4.34
LL2	0.068	0.078	1.73	1.98
LS1	.121 BSC		3.07 BSC	
LS2	.083 BSC		1.54 BSC	
LS3	.044 BSC		1.12 BSC	
LS4	.167 BSC		4.24 BSC	
Q1	0.030		0.76	

NOTES:

1. DIMENSIONING & TOLERANCING PER ASME Y14.5M-1994.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSIONS ARE SHOWN IN INCHES [MILLIMETERS].
4. STANDARD FINAL FINISH ON ALL TERMINALS IS SOLDER ALLOY 63%Sn 37%Pb.

IOR HiRel
An Infineon Technologies Company

TITLE: SMD-0.2 ENHANCED
OUTLINE WITH CERAMIC LID

DRAWING NO.
D101029G-WEB

REV E4