






# Case outline



SYMBOL	DIMENSIONS					
	MILLIMETERS			INCHES		
	MO-150AH			MO-150AH		
	MIN	NOM	MAX	MIN	NOM	MAX
A	1.73	1.86	2.00	.068	.073	.078
A1	0.05	0.13	0.20	.002	.005	.008
A2	1.65	1.75	1.85	.065	.069	.073
b	0.22	0.30	0.38	.009	.012	.015
c	0.09	0.15	0.25	.004	.006	.010
D	7.90	8.20	8.50	.311	.323	.334
E	7.80 BSC			.307		
E1	5.00	5.30	5.60	.197	.209	.221
e	0.65 BSC			.026 BSC		
L	0.55	0.75	0.95	.022	.030	.037
L1	0.25 BSC			.010 BSC		
$\alpha$	0°	4°	8°	0°	4°	8°
aaa	0.10			.004		
bbb	0.15			.006		
ccc	0.20			.008		



## MINIMUM RECOMMENDED FOOTPRINT



## NOTES

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
2. DIMENSIONS ARE SHOWN IN MILLIMETERS AND INCHES.
3. CONTROLLING DIMENSION: MILLIMETER.
4. DATUM PLANE H IS LOCATED AT THE BOTTOM OF THE MOLD PARTING LINE COINCIDENT WITH WHERE THE LEAD EXITS THE BODY.
5. DATUM B AND C TO BE DETERMINED AT DATUM PLANE H.
6. DIMENSIONS D AND E1 ARE DETERMINED AT DATUM PLANE H.
7. L IS THE LEAD LENGTH FOR SOLDERING TO A SUBSTRATE.
8. OUTLINE CONFORMS TO JEDEC OUTLINE MO-150AH.

**24-Lead SSOP**

01 6076 01  
01 5537 01 MO-150AH